

4. Figures below show the unit connected to dual 3/8" ID tubing.



Placentia, California




Fig. 4
Mount inside 1-1/2-inch
standpipe




Fig. 5
Installed on top rim of
standpipe inside wall box




Fig. 6
Secure Inlet Tubing




Use plastic loop clamps
or similar (not included)



Model:
AG100-003

UNIVERSAL 3-PORT AIR GAP FOR 3/8-inch ID TUBING

Maximum flow rate 5.2 GPM total.
Inlet C Maximum flow rate 0.5 GPM.




Part No.
AG100-003

AG100-003

Installation Procedures

LIST OF PARTS ENCLOSED

1 – Three Port Air Gap.....



AG100-003 Three Port Air Gap

- Three 3/8-inch OD inlets for regular or reinforced tubing with a 3/8-inch ID.
- Installs in both 1-1/2-inch and 2-inch standpipes
- Easy to install and maintain
- Standpipes can accommodate up to 3 units at a time
- UPC® listed and tested for compliance with UPC and IPC

INSTALLATION INSTRUCTIONS

1. The AG100-003 is truly unique and permits quick and easy mounting over the top lip or inside the standpipe. It works well with exposed standpipes or within recessed wall boxes.

The AG100-003 fits on the outer rim or inside of 1-1/2-inches or 2-inches standpipe (metal or plastic). Always mount vertically at the top of the standpipe as pictured in Fig.1 and Fig. 2

2. AG100-003 unit has three ports designed to fit 3/8-inch ID tubing.
3. Secure drainage tubing with an appropriate clamp to avoid leaking. Do not over tighten as not to damage the inlet ports.
4. Secure inlet tubes to wall using plastic clamps. Clamps are not included. Fig. 6.




Fig.1
Installation in 2-inch standpipe




Fig. 2
Installation in 1-1/2 inch standpipe




Fig.3